

Bring your vision up to par

Mid Range 



Lenstec (Barbados) Inc.,
 Airport Commercial Centre, Pilgrim Road,
 Christ Church, BB17092, Barbados
 Phone: +1 (246) 420-6795 Fax: +1 (246) 420-6797
 Email: lenstecbarbados@lenstec.com

Lenstec Barbados Inc.
 Lenstec House, Lakeside Calder Island Way
 Wakefield, West Yorkshire, WF27AW
 Phone: +44 (0) 1924 382 678 Fax: +44 (0) 1924 831 080
 Email: lenstecuk@lenstec.com

World Headquarters: Lenstec Inc
 1765 Commerce Ave. N.
 St. Petersburg, FL 33716, USA
 Phone: +1 (727) 571-2272 Fax: +1 (727) 571-1792



The Active Lens For Active Lifestyles.



Far Range 

Close Range 



What Are Cataracts?

As we get older the eye's natural lens becomes clouded, hardened, and loses its elasticity; therefore, everyone eventually experiences a gradual decrease of vision. The lens is responsible for focusing light and producing clear sharp images.

Common symptoms of cataracts are: halos around lights, sensitivity to sunlight, and blurry vision, especially when reading or driving at night.



Tetraflex HD™ Active Lifestyle

Lens replacement surgery is all about restoring youthful vision. Tetraflex HD™ replaces your natural lens and imitates the eye's natural function. Actively moving with your eye muscles to experience near, mid, and far vision.



Full Range of Vision. Effortlessly

In the past, cataract surgery was only able to treat a patient's cataracts, so patients would still be dependent on glasses for most of their daily activities, especially for close up and intermediate distances. Tetraflex HD™ will correct for more than just your cataracts. Tetraflex HD™ allows you to experience near, mid, and far vision effortlessly. Tetraflex HD™ provides you with the opportunity to rediscover true eyesight potential.

Bi-Aspheric Advantage

Bi-Aspheric lenses mimic the natural focusing ability of the human eye. These lenses are used in high-end binoculars and cameras because they allow wider peripheral vision, greater visual range, depth of focus and improved night vision without halo and glare. Tetraflex HD™ adapts this technology and allows surgeons the ability to enhance your visual outcome by precisely customizing your treatment plan to ensure the best possible outcome.

Precision Accuracy

The Tetraflex HD™ has micro-prescription optics, with smaller lens power increments with nearly 300% tighter tolerance than industry standard. The Tetraflex HD™ is manufactured with proprietary technology that produces super-accurate lens power labeling.



Quick Recovery. Safe Results.

With virtually no down time, you will be able to enjoy a quick recovery. You should be able to return to your normal activities within just a few short days

How Active Is Your Lifestyle?

Only your Ophthalmologist can determine if you are a good candidate for Tetraflex HD™. Speak with your Ophthalmologist today about this exciting technology and if the Tetraflex HD™ is right for you.

To learn more about Tetraflex HD™, visit us at www.lenstec.com

